


The latest development for compression fittings results in a termination at least as strong as the rated breaking load of the wire rope. The unique star shaped Crown Ring positions and holds the wire strands in place, eliminating the requirement for awkward wire end bending. The shallow angled cone establishes direct mechanical grip on the core and all outer strands. Stainless steel grade EN10088 1.4404 (316) is used on all parts with the exception of the crown ring which is manufactured from Aluminium Bronze. No sealant or packing is required.

Compression Terminal Extender



Metric Wire - 3mm to 26mm



The Hi-MOD Compression Terminal Extender is a “one-fits-all” component which will allow a damaged swage terminal to be replaced quickly and easily. The extender makes up approximately 15 wire diameters in length and can even be extended further by joining extenders together. The extender is a temporary fix and damaged wires should be replaced as soon as possible.



The compression terminal extender must be used in conjunction with a compression eye, stud, fork or toggle.



PRODUCT CODE	WIRE	EXT	A/F-L	A/F-B	OD	WEIGHT
CTX03	3mm	45mm	6mm	9.5mm	11mm	24g
CTX04	4mm	60mm	8mm	11mm	13mm	39g
CTX05	5mm	75mm	9mm	14mm	16mm	100g
CTX06	6mm	90mm	11mm	17mm	19mm	131g
CTX07	7mm	105mm	13mm	20mm	22mm	207g
CTX08	8mm	120mm	16mm	22mm	26mm	311g
CTX10	10mm	150mm	17mm	26mm	30mm	536g
CTX12	12mm	180mm	22mm	32mm	39mm	1023g
CTX14	14mm	210mm	24mm	36mm	44mm	1637g
CTX16	16mm	240mm	28mm	40mm	48mm	2136g
CTX19	19mm	285mm	32mm	44mm	51mm	2807g
CTX22	22mm	330mm	34mm	52mm	57mm	4098g
CTX26	26mm	390mm	44mm	64mm	77mm	8591g

What is a Compression Terminal Extender and How Does It Work?

The Hi-MOD Compression Terminal Extender allows you to repair a wire which has broken at the swage terminal without having to replace the whole wire. The increased length of the terminal extender makes up the reduction in wire length. The Compression Terminal Extender is a swageless terminal which allows the repair to be made quickly and easily anywhere. The extender must be used in conjunction with a fork, eye, stud or toggle compression terminal.